

K74 coating system C4 H NDFT 240µm

Contents

1	Area of application	2
1.1	Corrosivity category	2
1.2	Protection lifetime	2
1.3	Examples for the associated environment according to international standards	2
2	Coating system	3
3	Pretreatment of steel and cast-iron components for applying primer	4
3.1	Removing surface irregularities	4
3.2	Surface preparation before applying primer	4

Department responsible LDA M NMA M EN	Technical reference Haering	Created by Hausruckinger	Approved by Verhoeven	Project Standard		
SIEMENS	Document type K74 coating system C4 H NDFT 240µm	Document status Released		Customer tag		
	SIMOTICS HV C/M/HP, HS-synchron/modyn, Rolling, Mining, SIGENTICS, SIGENTICS M	Document number A5E52198860B				
© Siemens 2022		Rev. AA	Edition date (YYYY-MM-DD) 2022-11-16	Language en	Page 1/4	

1 Area of application

1.1 Corrosivity category

C4 (ISO 12944)

1.2 Protection lifetime¹

H (High); 15 to 25 years

1.3 Examples for the associated environment according to international standards

ISO 12944

Outdoors: Industrial atmosphere and coastal atmosphere with moderate salt levels

Indoors: Chemical plants, swimming pools, shipyards and ports close to the coast

ISO 9223

Outdoors: Moderate climatic zone, atmospheric environment with high air pollution (SO²: 30 ... 90 µg m⁻³) or with substantial influence as a result of chlorides, e.g. urban areas with air pollution, industrial areas, coastal areas, not in the area of salt water spray, heavy exposure to de-icing salts. Subtropical and tropical climatic zones, atmospheres with moderate pollution levels

Indoors: Rooms with frequent condensation and high air pollution from production processes, e.g. industrial plants, swimming pools

This coating system can also be used for:

Corrosivity category	Protection lifetime
C3	VH (Very high); over 25 years
C5	M (Medium); 7 to 15 years

¹The protection duration does not represent a "warranty time" (ISO 12944-1 and -5). Rather, it should help customers define a maintenance/repair program. The specified "expected protection lifetime" represents the predicted protection lifetime of this coating system for the environmental conditions according to ISO 12944-2. The suitability and classification of the protection lifetime of the coating system for the particular corrosivity category is based on the results from load tests according to ISO 12944-6.

Department responsible LDA M NMA M EN	Technical reference Haering	Created by Hausruckinger	Approved by Verhoeven	Project Standard		
SIEMENS	Document type K74 coating system C4 H NDFT 240µm	Document status Released		Customer tag		
	SIMOTICS HV C/M/HP, HS-synchron/modyn, Rolling, Mining, SIGENTICS, SIGENTICS M	Document number A5E52198860B				
© Siemens 2022		Rev. AA	Edition date (YYYY-MM-DD) 2022-11-16	Language en	Page 2/4	

2 Coating system

The coating system has the following structure:

Primer²

Coating compound	1-component epoxy ester/acrylic resin dip primer ³ 2-component epoxy resin spray primer
NDFT coating thickness ⁴	60 µm

Intermediate coat⁵

Coating compound	2-component epoxy resin coating
NDFT coating thickness ⁴	100 µm

Topcoat⁵

Coating compound	2-component acrylic polyurethane coating
NDFT coating thickness ⁴	80 µm
Color	RAL 7030 (other colors optionally available)

Total paint coat thickness⁴ 240 µm

If not ordered differently, stainless steel, aluminum, non-ferrous metals and plastics are not coated.

²Also on inner surfaces, with the exception of machined surfaces, for example shafts and active parts.

³Only for complex cast parts

⁴Specified "nominal dry film thickness" (NDFT)

⁵If not ordered differently, then these coatings are only applied to external surfaces. For production-related reasons, they can also be found on inner surfaces.

Department responsible LDA M NMA M EN	Technical reference Haering	Created by Hausruckinger	Approved by Verhoeven	Project Standard		
SIEMENS	Document type K74 coating system C4 H NDFT 240µm		Document status Released		Customer tag	
	SIMOTICS HV C/M/HP, HS-synchron/modyn, Rolling, Mining, SIGENTICS, SIGENTICS M		Document number A5E52198860B			
© Siemens 2022			Rev. AA	Edition date (YYYY-MM-DD) 2022-11-16	Language en	Page 3/4

3 Pretreatment of steel and cast-iron components for applying primer

3.1 Removing surface irregularities

Preparation grade P2 for weld seams, edges and other surfaces (ISO 8501-3)

3.2 Surface preparation before applying primer

Cast-iron components Blasted with round or angular abrasives
 SCRATA evaluation:⁶ A3, B1, C2, H1
 Average grade of surface roughness acc. to ISO 8503-2
 Parts free of:Dust⁷, Grease, Contaminants⁸

Steel parts Blasted with round or angular abrasives
 Wall thickness \geq 3 mm Grade Sa 2 1/2 (ISO 8501-1)
 Average grade of surface roughness acc. to ISO 8503-2
 Parts free of:Dust⁷, Grease, Contaminants⁸

Steel parts Surface preparation grade St 3 (ISO 8501-1)
 Wall thickness < 3 mm Parts free of:Dust⁷, Grease, Contaminants⁸

⁶Cast surfaces are assessed according to ISO 8503-2. SCRATA comparison standards are used for special local effects on caste surfaces.

⁷Particle size Class \leq 2 / dust quantity characteristic value \leq 2 (ISO 8502-3). Light up to average discoloring of the adhesive tape as a result of graphite particles for cast iron parts is unavoidable and permissible.

⁸Water soluble contaminants: Maximum: 40 mg m⁻² NaCl (ISO 8502-6 and ISO 8502-9)

Department responsible LDA M NMA M EN	Technical reference Haering	Created by Hausruckinger	Approved by Verhoeven	Project Standard			
SIEMENS	Document type K74 coating system C4 H NDFT 240µm		Document status Released		Customer tag		
	SIMOTICS HV C/M/HP, HS-synchron/modyn, Rolling, Mining, SIGENTICS, SIGENTICS M		Document number A5E52198860B				
© Siemens 2022			Rev. AA	Edition date (YYYY-MM-DD) 2022-11-16	Language en	Page 4/4	